# Accessories


### **Automatic Air and Vacuum Valve**



## Model 9922 Water Tapping Set for air valve set 992







### Features

Can be used instead of the air release valve in an air valve set ( Model no. 992 ). Use Water tapping set for flushing or sampling device under pressure.

Max. operating pressure: 250 psi / 17.2 bar

Pipe, screw connection and elbow: Steel

Fitting: GJL-250 ( GG-25 ), fluidized bed epoxy powder coated

Push fitting: POM, NBR Ball valve: brass

### Advantages

Installation and dismantling under pressure

Use for flushing and venting after initial start-up and/or filling of pipelines

Controlled water tapping via ball valve

Pressure testing

| Туре    | Pipe cover depth of air valve set | Overall Height<br>air valve set | Weight<br>lbs. / kg |
|---------|-----------------------------------|---------------------------------|---------------------|
| Plug-in | 3.3 ft                            | 2.5 ft                          | 12.3 lbs.           |
|         | 1m                                | 755 mm                          | 5,6 Kg              |

Other dimensions on request!